



GPR101 Antibody

CATALOG NUMBER: 70-538

Specifications

SPECIES REACTIVITY:	Human, Mouse
TESTED APPLICATIONS:	ELISA, IF, IHC, WB
APPLICATIONS:	ELISA, IF, IHC-P (1:100), WB
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	GPR101 Antibody detects endogenous levels of total GPR101 protein.
IMMUNOGEN:	Synthetic peptide from human GPR101.
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Immunoaffinity Chromatography
BUFFER:	PBS (without Mg2+, Ca2+), pH 7.4, 150 mM sodium chloride, 0.02% sodium azide, 50% glycerol
STORAGE CONDITIONS:	Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Polyclonal
ISOTYPE:	IgG
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	GPR101, G protein-coupled receptor 101, GPCR6
ACCESSION NO.:	Q96P66
PROTEIN GI NO.:	48474929
OFFICIAL SYMBOL:	GPR101
GENE ID:	83550

Background

FOR RESEARCH USE ONLY

December 13, 2016