



IRX3 Antibody

CATALOG NUMBER: 70-539

Specifications

SPECIES REACTIVITY:	Human, Mouse
TESTED APPLICATIONS:	ELISA, IHC
APPLICATIONS:	ELISA, IHC-P (1:200)
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	IRX3 Antibody detects endogenous levels of total IRX3 protein.
IMMUNOGEN:	Synthetic peptide from human IRX3.
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Immunoaffinity Chromatography
BUFFER:	PBS (without Mg2+, Ca2+), pH 7.4, 150 mM sodium chloride, 0.02% sodium azide, 50% glycerol
STORAGE CONDITIONS:	Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Polyclonal
ISOTYPE:	IgG
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	IRX3, Homeodomain protein IRXB1, IRXB1, Iroquois homeobox 3, Iroquois homeobox protein 3, IRX-1
ACCESSION NO.:	P78415
PROTEIN GI NO.:	47117874
OFFICIAL SYMBOL:	IRX3
GENE ID:	79191

Background

FOR RESEARCH USE ONLY

December 13, 2016