



ISG15 Antibody

CATALOG NUMBER: 70-542

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IHC, WB
APPLICATIONS:	ISG15 Antibody can be used for ELISA starting at 1:1000, and Immunohistochemistry in paraffin embedded tissues starting at 10 ug/mL,
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	KLH-conjugated synthetic peptide between amino acids 31-61 from N-terminal region of human ISG15.
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Protein G Column
BUFFER:	PBS, 0.09% sodium azide
CONCENTRATION:	0.25 mg/ml
STORAGE CONDITIONS:	Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Polyclonal
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	ISG15, HUCRP, IFI15, ISG15 ubiquitin-like modifier, G1P2, IP17, Ubiquitin-like protein ISG15, UCRP
ACCESSION NO.:	P05161
PROTEIN GI NO.:	52001470
OFFICIAL SYMBOL:	ISG15
GENE ID:	9636

Background

FOR RESEARCH USE ONLY

December 13, 2016