



HNRNPA1 / HnRNP A1 Antibody

CATALOG NUMBER: 70-558

Specifications

SPECIES REACTIVITY:	Human, Mouse, Rat
TESTED APPLICATIONS:	ELISA, IF, IHC, WB
APPLICATIONS:	ELISA, IF, IHC-P (1:200), WB
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	hnRNP A1 Antibody detects endogenous levels of total hnRNP A1 protein.
IMMUNOGEN:	Synthetic peptide from human hnRNP A1.
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Immunoaffinity Chromatography
BUFFER:	PBS (without Mg2+, Ca2+), pH 7.4, 150 mM sodium chloride, 0.02% sodium azide, 50% glycerol
STORAGE CONDITIONS:	Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Polyclonal
ISOTYPE:	IgG
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	HNRNPA1, HNRPA1L3, HnRNP A1, HnRNP A1-like 3, HnRNP core protein A1, Helix-destabilizing protein, HNRPA1, HnRNP core protein A1-like 3, HnRNP-A1
ACCESSION NO.:	P0C7M2
PROTEIN GI NO.:	190360152
OFFICIAL SYMBOL:	HNRNPA1
GENE ID:	3178

Background

FOR RESEARCH USE ONLY

December 13, 2016