



CLDN1 / Claudin 1 Antibody

CATALOG NUMBER: 70-623

Specifications

SPECIES REACTIVITY:	Human, Mouse, Rat
TESTED APPLICATIONS:	ELISA, IHC, WB
APPLICATIONS:	ELISA, IHC-P (1:200), WB
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	Claudin 1 Antibody detects endogenous levels of total Claudin 1 protein.
IMMUNOGEN:	Synthetic peptide from human Claudin 1.
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Immunoaffinity Chromatography
BUFFER:	PBS (without Mg2+, Ca2+), pH 7.4, 150 mM sodium chloride, 0.02% sodium azide, 50% glycerol
STORAGE CONDITIONS:	Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Polyclonal
ISOTYPE:	IgG
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	CLDN1, Claudin-1, Claudin 1, ILVASC, SEMP1, CLD1
ACCESSION NO.:	O95832
PROTEIN GI NO.:	6685283
OFFICIAL SYMBOL:	CLDN1
GENE ID:	9076

Background

FOR RESEARCH USE ONLY

December 13, 2016