



RXRG Antibody

CATALOG NUMBER: 70-685

Specifications

SPECIES REACTIVITY:	Human, Mouse, Rat
TESTED APPLICATIONS:	IHC
APPLICATIONS:	RXRG Antibody can be used for Immunohistochemistry in paraffin embeded tissues starting at 1:100.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Synthetic peptide from N-Terminus of mouse RXR gamma.
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Immunoaffinity Chromatography
BUFFER:	10 mM PBS, pH 7.4, BSA, sodium azide.
STORAGE CONDITIONS:	Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Polyclonal
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	RXRG, NR2B3, Retinoid X receptor gamma, Retinoid X receptor, gamma, RXR-gamma, RXRC
ACCESSION NO.:	P48443
PROTEIN GI NO.:	1350913
OFFICIAL SYMBOL:	RXRG
GENE ID:	6258

Background

FOR RESEARCH USE ONLY

December 13, 2016