



LDHA Antibody, Monoclonal

CATALOG NUMBER: 70-136

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IHC, WB
APPLICATIONS:	LDHA Monoclonal Antibody can be used for immunohistochemistry (tested on parafin embedded tissues) starting at 20 ug/mL and Western Blot starting at 1:1000.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	Anti-LDHA recognizes recombinant protein LDHA.
IMMUNOGEN:	Native human ALB / Albumin.
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Affinity Purified
PHYSICAL STATE:	Liquid
BUFFER:	Citrate-Tris-HCl buffer, pH 7.0, 0.02% Proclin 300
STORAGE CONDITIONS:	LDHA Monoclonal antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG1
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	LDHA, LDH muscle subunit, LDH1, Lactate dehydrogenase M, LDH-M, GSD11, Lactate dehydrogenase A, LDH-A, LDHM, PIG19, Proliferation-inducing gene 19
ACCESSION NO.:	P00338
PROTEIN GI NO.:	126047
OFFICIAL SYMBOL:	LDHA
GENE ID:	3939

Background

FOR RESEARCH USE ONLY

December 13, 2016