



PTRF Antibody

CATALOG NUMBER: 70-372

Specifications

SPECIES REACTIVITY:

TESTED APPLICATIONS:

APPLICATIONS: PTRF Antibody can be used for ELISA starting at 1:1000, and Immunohistochemistry in paraffin embedded tissues starting at 5 ug/mL,

USER NOTE: Optimal dilutions for each application to be determined by the researcher.

IMMUNOGEN: KLH-conjugated synthetic peptide between amino acids 1-30 from N-terminal region of human PTRF.

HOST SPECIES: Rabbit

Properties

PURIFICATION: Ammonium Sulfate Precipitation

BUFFER: PBS, 0.09% sodium azide

CONCENTRATION: 0.25 mg/ml

STORAGE CONDITIONS: Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.

CLONALITY: Polyclonal

CONJUGATE: Unconjugated

Additional Info

ALTERNATE NAMES: PTRF, Cavin-1, CAVIN1, CAVIN, CGL4, FKSG13, TTF-I interacting peptide 12

ACCESSION NO.: Q6NZI2

PROTEIN GI NO.: 56749614

OFFICIAL SYMBOL: PTRF

GENE ID: 284119

Background

FOR RESEARCH USE ONLY

December 13, 2016