




## FOXA1 Antibody [2D7]

CATALOG NUMBER: 51-961



Immunohistochemistry of human prostate tissue stained using FOXA1 Monoclonal Antibody.

### Specifications

<b>SPECIES REACTIVITY:</b>	Human
<b>TESTED APPLICATIONS:</b>	ELISA, IHC, WB
<b>APPLICATIONS:</b>	FOXA1 antibody can be used in Western Blot starting at 1 - 3 ug/mL, and immunohistochemistry starting at 10 ug/mL.
<b>USER NOTE:</b>	Optimal dilutions for each application to be determined by the researcher.
<b>IMMUNOGEN:</b>	FOXA1 (NP_004487, 367 a.a. ~ 473 a.a) partial recombinant protein with GST tag. MW of the GST tag alone is 26 KDa.
<b>HOST SPECIES:</b>	Mouse

### Properties

<b>PURIFICATION:</b>	Protein A Column
<b>PHYSICAL STATE:</b>	Liquid
<b>BUFFER:</b>	PBS, pH 7.2
<b>STORAGE CONDITIONS:</b>	Aliquot and store FOXA1 antibody at -20 °C or -80 °C. As with all antibodies avoid freeze/thaw cycles.
<b>CLONALITY:</b>	Monoclonal
<b>ISOTYPE:</b>	IgG2a,k
<b>CONJUGATE:</b>	Unconjugated

### Additional Info

<b>ALTERNATE NAMES:</b>	FOXA1, Forkhead box A1, Forkhead box protein A1, HNF-3-alpha, HNF-3A, TCF-3A, TCF3A, HNF3A, Transcription factor 3A
<b>ACCESSION NO.:</b>	P55317
<b>PROTEIN GI NO.:</b>	296434509
<b>OFFICIAL SYMBOL:</b>	FOXA1
<b>GENE ID:</b>	3169

FOR RESEARCH USE ONLY

December 13, 2016