



HMGB3 Antibody

CATALOG NUMBER: 70-348

Specifications

SPECIES REACTIVITY:	Bovine, Chicken, Chimpanzee, Dog, Horse, Human, Mouse
TESTED APPLICATIONS:	IHC, WB
APPLICATIONS:	HMGB3 Antibody can be used for Immunohistochemistry in paraffin embedded tissues starting at 10 ug/mL, and Western Blotting starting at 0.5 - 1 ug/mL.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	Human HMGB3.
IMMUNOGEN:	A portion of amino acids 150-200 of human HMGB3.
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Immunoaffinity Chromatography
BUFFER:	PBS, 0.05% BSA, 0.05% sodium azide
CONCENTRATION:	0.5 mg/ml
STORAGE CONDITIONS:	Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Polyclonal
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	HMGB3, High mobility group protein 2a, High mobility group protein B3, HMG-2a, High mobility group box 3, High mobility group protein 4, High-mobility group box 3, HMG-4, HMG2A, HMG4
ACCESSION NO.:	O15347
PROTEIN GI NO.:	85701353
OFFICIAL SYMBOL:	HMGB3
GENE ID:	3149

Background

FOR RESEARCH USE ONLY

December 13, 2016