



ANXA6 / Annexin VI Antibody

CATALOG NUMBER: 70-433

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IF, IHC, WB
APPLICATIONS:	ELISA, IF, IHC-P (1:100), WB
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	Annexin A6 Antibody detects endogenous levels of total Annexin A6 protein.
IMMUNOGEN:	Synthetic peptide from human Annexin A6.
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Immunoaffinity Chromatography
BUFFER:	PBS (without Mg2+, Ca2+), pH 7.4, 150 mM sodium chloride, 0.02% sodium azide, 50% glycerol
STORAGE CONDITIONS:	Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Polyclonal
ISOTYPE:	IgG
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	ANXA6, 67 kDa calelectrin, Annexin VI (p68), Annexin A6, Annexin VI, ANX6, Calcium-binding protein p68, Calelectrin, CBP68, Chromobindin-20, Calphobindin-II, Lipocortin VI, p70, Protein III, Annexin-6, Calphobindin II, CPB-II, p68
ACCESSION NO.:	P08133
PROTEIN GI NO.:	113962
OFFICIAL SYMBOL:	ANXA6
GENE ID:	309

Background

FOR RESEARCH USE ONLY

December 13, 2016