



HES1 Antibody

CATALOG NUMBER: 70-613

Specifications

APPLICATIONS:	HES1 Antibody can be used for ELISA starting at 1:80000, and Immunohistochemistry in paraffin embedded tissues starting at 2.5 ug/mL,
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Synthetic peptide
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Affinity Purified
BUFFER:	PBS (without Mg2+, Ca2+), pH 7.4, 150 mM sodium chloride, 0.02% sodium azide, 50% glycerol
CONCENTRATION:	1 mg/ml
STORAGE CONDITIONS:	Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Polyclonal
ISOTYPE:	IgG
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	HES1, BHLHb39, HHL, HL, Hairy and enhancer of split 1, Hairy homolog, HRY, Hairy homolog (Drosophila), Transcription factor HES-1, Hairy-like protein, HES-1
ACCESSION NO.:	Q14469
PROTEIN GI NO.:	3913825
OFFICIAL SYMBOL:	HES1
GENE ID:	3280

Background

FOR RESEARCH USE ONLY

December 13, 2016