



SYK Antibody [12E3]

CATALOG NUMBER: 70-077

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	IHC, IP, WB
APPLICATIONS:	IHC-P (1:400), IP, WB (1:1000)
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Synthetic peptide (a.a. 313-330).
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Ammonium Sulfate Precipitation
PHYSICAL STATE:	Liquid
BUFFER:	HEPES with 0.15M NaCl, 0.01% BSA, 0.03% sodium azide, and 50% glycerol
STORAGE CONDITIONS:	SYK Monoclonal antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles. Store undiluted.
CLONALITY:	Monoclonal
ISOTYPE:	IgG2b,k
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	SYK, p72syk, Spleen tyrosine kinase, Syk protein-tyrosine kinase, Tyrosine-protein kinase SYK, p72-Syk
ACCESSION NO.:	P43405
PROTEIN GI NO.:	1174527
OFFICIAL SYMBOL:	SYK
GENE ID:	6850

Background

FOR RESEARCH USE ONLY

December 13, 2016