



MAPK8 Antibody [2F3]

CATALOG NUMBER: 70-168

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IHC, IP, WB
APPLICATIONS:	MAPK8 Monoclonal Antibody can be used for immunohistochemistry (tested on parafin embedded tissues) starting at 5 ug/mL and Western Blot starting at 1:500 - 1:1000.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Recombinant protein
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein A Column
PHYSICAL STATE:	Liquid
BUFFER:	PBS, pH 7.2
STORAGE CONDITIONS:	MAPK8 Monoclonal antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG2a,k
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	MAPK8, JNK, JNK1, JNK1A2, JNK-46, MAP kinase 8, PRKM8, SAPK1, SAPK1c, MAPK 8, C-Jun N-terminal kinase 1, JNK21B1/2, JUN N-terminal kinase
ACCESSION NO.:	P45983
PROTEIN GI NO.:	2507195
OFFICIAL SYMBOL:	MAPK8
GENE ID:	5599

Background

FOR RESEARCH USE ONLY

December 13, 2016