



CEACAM1 Antibody [2F6]

CATALOG NUMBER: 70-169

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IHC, WB
APPLICATIONS:	CEACAM1 Monoclonal Antibody can be used for immunohistochemistry (tested on paraffin embedded tissues) starting at 10 ug/mL and Western Blot starting at 1:500 - 1:1000.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Recombinant protein
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein A Column
PHYSICAL STATE:	Liquid
BUFFER:	PBS, pH 7.2
STORAGE CONDITIONS:	CEACAM1 Monoclonal antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG1,k
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	CEACAM1, Antigen CD66, BGP1, Biliary glycoprotein 1, CD66a, BGP-1, BGP, BGPI, CD66a antigen
ACCESSION NO.:	P13688
PROTEIN GI NO.:	399116
OFFICIAL SYMBOL:	CEACAM1
GENE ID:	634

Background

FOR RESEARCH USE ONLY

December 13, 2016