



NPY Antibody [3H2]

CATALOG NUMBER: 70-171

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IHC, WB
APPLICATIONS:	NPY Monoclonal Antibody can be used for immunohistochemistry (tested on parafin embedded tissues) starting at 5 ug/mL and Western Blot starting at 1:500 - 1:1000.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Recombinant protein
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein A Column
PHYSICAL STATE:	Liquid
BUFFER:	PBS, pH 7.2
STORAGE CONDITIONS:	NPY Monoclonal antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG1,k
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	NPY, Pro-neuropeptide Y, Neuropeptide Y, PYY4
ACCESSION NO.:	P01303
PROTEIN GI NO.:	128117
OFFICIAL SYMBOL:	NPY
GENE ID:	4852

Background

FOR RESEARCH USE ONLY

December 13, 2016