



PYGM Antibody [2C4]

CATALOG NUMBER: 70-182

Specifications

SPECIES REACTIVITY:	Human, Mouse, Rat
TESTED APPLICATIONS:	ELISA, IHC, WB
APPLICATIONS:	PYGM Monoclonal Antibody can be used for immunohistochemistry (tested on parafin embedded tissues) starting at 5 ug/mL.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Recombinant protein
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein A Column
PHYSICAL STATE:	Liquid
BUFFER:	PBS, pH 7.2
STORAGE CONDITIONS:	PYGM Monoclonal antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG1,k
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	PYGM, GPMM, Myophosphorylase, Phosphorylase, glycogen muscle
ACCESSION NO.:	P11217
PROTEIN GI NO.:	3041717
OFFICIAL SYMBOL:	PYGM
GENE ID:	5837

Background

FOR RESEARCH USE ONLY

December 13, 2016