



PBX3 Antibody [1A11]

CATALOG NUMBER: 70-208

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IHC, WB
APPLICATIONS:	PBX3 Monoclonal Antibody can be used for immunohistochemistry (tested on paraffin embedded tissues) starting at 5 ug/mL.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	PBX3 (NP_006186, 342 a.a. ~ 435 a.a) partial recombinant protein with GST tag. MW of the GST tag alone is 26 KDa.
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein A Column
PHYSICAL STATE:	Liquid
BUFFER:	PBS, pH 7.2
STORAGE CONDITIONS:	PBX3 Monoclonal antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG2a,k
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	PBX3, Pre-B-cell leukemia homeobox 3, Homeobox protein PBX3
ACCESSION NO.:	P40426
PROTEIN GI NO.:	730281
OFFICIAL SYMBOL:	PBX3
GENE ID:	5090

Background

FOR RESEARCH USE ONLY

December 13, 2016