



TOP2A Antibody [Ki-S1]

CATALOG NUMBER: 70-293

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	IHC
APPLICATIONS:	TOP2A antibody can be used for staining paraffin embeded tissues starting at 1:50.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Lysate of the human histiocytic leukemia cell line U937.
HOST SPECIES:	Mouse

Properties

STORAGE CONDITIONS:	Antibody is stable for 24 months when stored at 2-8°C.
CLONALITY:	Monoclonal
ISOTYPE:	IgG2a,k
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	TOP2A, DNA topoisomerase II, 170 kD, TOP2, DNA gyrase, DNA topoisomerase 2-alpha, TP2A
ACCESSION NO.:	P11388
PROTEIN GI NO.:	13959709
OFFICIAL SYMBOL:	TOP2A
GENE ID:	7153

Background

FOR RESEARCH USE ONLY

December 13, 2016