



HSP90 Alpha Antibody [Hyb-K41009]

CATALOG NUMBER: 70-315

Specifications

SPECIES REACTIVITY:	Human, Rat
TESTED APPLICATIONS:	ELISA, IHC, WB
APPLICATIONS:	HSP90 Alpha antibody can be used for staining paraffin embeded tissues starting at 10 ug/mL, and Western Blot starting at 1 ug/mL.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	Detects 90kD proteins corresponding to the molecular mass of hsp90alpha.
IMMUNOGEN:	Recombinant human Hsp90alpha.
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein G Column
STORAGE CONDITIONS:	Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG2a
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	HSP90A, HSPC1, HSPCA, Heat shock protein HSP 90-alpha, Heat shock 86 kDa, HSP 86, EL52, HSPN, LAP2, HSP86, Hsp89, Hsp90, HSP89A, HSP90N, HSPCAL1, HSPCAL4
ACCESSION NO.:	P07900
PROTEIN GI NO.:	92090606
OFFICIAL SYMBOL:	HSP90AA1
GENE ID:	3320

Background

FOR RESEARCH USE ONLY

December 13, 2016