



## HSP90 Antibody [Hyb-K41220A]

CATALOG NUMBER: 70-318

### Specifications

<b>SPECIES REACTIVITY:</b>	Human, Rat, S. pombe, Yeast
<b>TESTED APPLICATIONS:</b>	ELISA, IHC, WB
<b>APPLICATIONS:</b>	HSP90 antibody can be used for staining paraffin embedded tissues starting at 10 ug/mL, and Western Blot starting at 1 ug/mL.
<b>USER NOTE:</b>	Optimal dilutions for each application to be determined by the researcher.
<b>SPECIFICITY:</b>	Detects both HSP90 alpha and beta, at 90kD.
<b>IMMUNOGEN:</b>	Recombinant human Hsp90alpha.
<b>HOST SPECIES:</b>	Mouse

### Properties

<b>PURIFICATION:</b>	Protein G Column
<b>STORAGE CONDITIONS:</b>	Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
<b>CLONALITY:</b>	Monoclonal
<b>ISOTYPE:</b>	IgG2a
<b>CONJUGATE:</b>	Unconjugated

### Additional Info

<b>ALTERNATE NAMES:</b>	HSP90, Hsp86, Hspca, Heat shock protein HSP 90-alpha, Heat shock 86 kDa, HSP 86, Hsp90
<b>ACCESSION NO.:</b>	P82995
<b>PROTEIN GI NO.:</b>	122065208
<b>OFFICIAL SYMBOL:</b>	Hsp90aa1
<b>GENE ID:</b>	299331

### Background

FOR RESEARCH USE ONLY

December 13, 2016