



HSP90 Antibody [4F3.E8]

CATALOG NUMBER: 70-321

Specifications

| | |
|-----------------------------|---|
| SPECIES REACTIVITY: | Human, Mouse, Rat |
| TESTED APPLICATIONS: | ELISA, ICC, IHC, IP, WB |
| APPLICATIONS: | HSP90 antibody can be used for ICC, staining paraffin embedded tissues starting at 10 ug/mL, and Western Blot starting at 1:2000. |
| USER NOTE: | Optimal dilutions for each application to be determined by the researcher. |
| SPECIFICITY: | Detects both a and B forms of hsp90 equally well. |
| IMMUNOGEN: | Recombinant Human Hsp90 purified from E. coli. |
| HOST SPECIES: | Mouse |

Properties

| | |
|----------------------------|---|
| PURIFICATION: | Protein G Column |
| STORAGE CONDITIONS: | Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles. |
| CLONALITY: | Monoclonal |
| ISOTYPE: | IgG1 |
| CONJUGATE: | Unconjugated |

Additional Info

| | |
|-------------------------|--|
| ALTERNATE NAMES: | HSP90, HSP90A, HSPC1, HSPCA, Heat shock protein HSP 90-alpha, Heat shock 86 kDa, HSP 86, EL52, HSPN, LAP2, HSP86, Hsp89, Hsp90, HSP89A, HSP90N, HSPCAL1, HSPCAL4 |
| ACCESSION NO.: | P07900 / P08238 |
| PROTEIN GI NO.: | 92090606 |
| OFFICIAL SYMBOL: | HSP90AA1 / HSP90AB1 |
| GENE ID: | 3320 / 3326 |

Background

FOR RESEARCH USE ONLY

December 13, 2016