



SULT1A3 Antibody

CATALOG NUMBER: 70-382

Specifications

SPECIES REACTIVITY:	Human, Mouse, Rat
TESTED APPLICATIONS:	IHC, WB
APPLICATIONS:	SULT1A3 Antibody can be used for Immunohistochemistry in paraffin embedded tissues starting at 1:400, and Western Blotting starting at 1:2000,
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Recombinant human SULT1A3 purified from E. coli.
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Purified
BUFFER:	HEPES with 0.15M NaCl, 0.01% BSA, 0.03% sodium azide, and 50% glycerol
CONCENTRATION:	1 mg/ml
STORAGE CONDITIONS:	Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Polyclonal
ISOTYPE:	IgG
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	SULT1A3, Aryl sulfotransferase 1A3/1A4, HAST3, M-PST, Phenol sulfotransferase 1A5, STM, ST1A5, TL-PST, HAST, ST1A3/ST1A4, Sulfokinase, Sulfotransferase 1A3/1A4
ACCESSION NO.:	P50224
PROTEIN GI NO.:	1711609
OFFICIAL SYMBOL:	SULT1A3
GENE ID:	6818

Background

FOR RESEARCH USE ONLY

December 13, 2016