



DBI Antibody

CATALOG NUMBER: 70-383

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	IHC, IP, WB
APPLICATIONS:	DBI Antibody can be used for Immunohistochemistry in paraffin embeded tissues starting at 1:400, Immunoprecipitation and Western Blotting starting at 1:1000.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Recombinant human GST-fusion protein purified from E. coli.
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Purified
BUFFER:	HEPES with 0.15M NaCl, 0.01% BSA, 0.03% sodium azide, and 50% glycerol
CONCENTRATION:	1 mg/ml
STORAGE CONDITIONS:	Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Polyclonal
ISOTYPE:	IgG
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	DBI, ACBP, Acyl-CoA-binding protein, CCK-RP, Diazepam-binding inhibitor, ACBD1, GABA receptor modulator, EP, Endozepine
ACCESSION NO.:	P07108
PROTEIN GI NO.:	118276
OFFICIAL SYMBOL:	DBI
GENE ID:	1622

Background

FOR RESEARCH USE ONLY

December 13, 2016