



MPO Antibody

CATALOG NUMBER: 70-388

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	IHC, IP, WB
APPLICATIONS:	MPO Antibody can be used for Immunohistochemistry in paraffin embedded tissues starting at 1:200, Immunoprecipitation and Western Blotting starting at 1:2000.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Synthetic peptide from human MPO.
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Purified
BUFFER:	HEPES with 0.15M NaCl, 0.01% BSA, 0.03% sodium azide, and 50% glycerol
STORAGE CONDITIONS:	Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Polyclonal
ISOTYPE:	IgG
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	MPO, Myeloperoxidase precursor, Myeloperoxidase
ACCESSION NO.:	P05164
PROTEIN GI NO.:	129825
OFFICIAL SYMBOL:	MPO
GENE ID:	4353

Background

FOR RESEARCH USE ONLY

December 13, 2016