



SAA4 Antibody

CATALOG NUMBER: 70-400

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IHC
APPLICATIONS:	ELISA, IHC-P (1:100)
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	SAA4 Antibody detects endogenous levels of total SAA4 protein.
IMMUNOGEN:	Synthetic peptide from human SAA4.
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Immunoaffinity Chromatography
BUFFER:	PBS (without Mg2+, Ca2+), pH 7.4, 150 mM sodium chloride, 0.02% sodium azide, 50% glycerol
STORAGE CONDITIONS:	Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Polyclonal
ISOTYPE:	IgG
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	SAA4, CSAA, Serum amyloid A4, constitutive, Serum amyloid A-4 protein, C-SAA
ACCESSION NO.:	P35542
PROTEIN GI NO.:	296452894
OFFICIAL SYMBOL:	SAA4
GENE ID:	6291

Background

FOR RESEARCH USE ONLY

December 13, 2016