



OMG / OMGP Antibody

CATALOG NUMBER: 70-401

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IHC
APPLICATIONS:	ELISA, IHC-P (1:100)
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	OMG Antibody detects endogenous levels of total OMG protein.
IMMUNOGEN:	Synthetic peptide from human OMG.
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Immunoaffinity Chromatography
BUFFER:	PBS (without Mg2+, Ca2+), pH 7.4, 150 mM sodium chloride, 0.02% sodium azide, 50% glycerol
STORAGE CONDITIONS:	Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Polyclonal
ISOTYPE:	IgG
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	OMG, OMGP
ACCESSION NO.:	P23515
PROTEIN GI NO.:	129122
OFFICIAL SYMBOL:	OMG
GENE ID:	4974

Background

FOR RESEARCH USE ONLY

December 13, 2016