



RORA Antibody

CATALOG NUMBER: 70-411

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IHC, WB
APPLICATIONS:	ELISA, IHC-P (1:200), WB
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	RORA Antibody detects endogenous levels of total RORA protein.
IMMUNOGEN:	Synthetic peptide from human RORA.
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Immunoaffinity Chromatography
BUFFER:	PBS (without Mg2+, Ca2+), pH 7.4, 150 mM sodium chloride, 0.02% sodium azide, 50% glycerol
STORAGE CONDITIONS:	Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Polyclonal
ISOTYPE:	IgG
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	RORA, Nuclear receptor ROR-alpha, Nuclear receptor RZR-alpha, Roralpha, Transcription factor RZR-alpha, RAR-related orphan receptor A, ROR-alpha, ROR3, RZRA, NR1F1, ROR Alpha, RZR-ALPHA
ACCESSION NO.:	P35398
PROTEIN GI NO.:	548814
OFFICIAL SYMBOL:	RORA
GENE ID:	6095

Background

FOR RESEARCH USE ONLY

December 13, 2016