



TIMP4 Antibody

CATALOG NUMBER: 70-417

Specifications

SPECIES REACTIVITY:	Human, Mouse, Rat
TESTED APPLICATIONS:	ELISA, IHC, WB
APPLICATIONS:	ELISA, IHC-P (1:200), WB
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	TIMP4 Antibody detects endogenous levels of total TIMP4 protein.
IMMUNOGEN:	Synthetic peptide from human TIMP4.
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Immunoaffinity Chromatography
BUFFER:	PBS (without Mg2+, Ca2+), pH 7.4, 150 mM sodium chloride, 0.02% sodium azide, 50% glycerol
STORAGE CONDITIONS:	Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Polyclonal
ISOTYPE:	IgG
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	TIMP4, Metalloproteinase inhibitor 4, TIMP-4
ACCESSION NO.:	Q99727
PROTEIN GI NO.:	3915135
OFFICIAL SYMBOL:	TIMP4
GENE ID:	7079

Background

FOR RESEARCH USE ONLY

December 13, 2016