



Synuclein Antibody

CATALOG NUMBER: 70-418

Specifications

SPECIES REACTIVITY:	Human, Mouse, Rat
TESTED APPLICATIONS:	ELISA, IHC, WB
APPLICATIONS:	ELISA, IHC-P (1:100), WB
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	Synuclein-pan Antibody detects endogenous levels of total Synuclein protein.
IMMUNOGEN:	Synthetic peptide from human Synuclein.
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Immunoaffinity Chromatography
BUFFER:	PBS (without Mg2+, Ca2+), pH 7.4, 150 mM sodium chloride, 0.02% sodium azide, 50% glycerol
STORAGE CONDITIONS:	Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Polyclonal
ISOTYPE:	IgG
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	NACP, PARK1, Alpha-synuclein, Non-A beta component of AD amyloid, PD1, PARK4
ACCESSION NO.:	P37840
PROTEIN GI NO.:	586067
OFFICIAL SYMBOL:	SNCA
GENE ID:	6622

Background

FOR RESEARCH USE ONLY

December 13, 2016