



CCNE1 / Cyclin E1 Antibody

CATALOG NUMBER: 70-446

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IF, IHC
APPLICATIONS:	ELISA, IF, IHC-P (1:100)
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	Cyclin E1 Antibody detects endogenous levels of total Cyclin E1 protein.
IMMUNOGEN:	Synthetic peptide from human Cyclin E1.
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Immunoaffinity Chromatography
BUFFER:	PBS (without Mg2+, Ca2+), pH 7.4, 150 mM sodium chloride, 0.02% sodium azide, 50% glycerol
STORAGE CONDITIONS:	Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Polyclonal
ISOTYPE:	IgG
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	CCNE1, Cyclin E1, CCNE, Cyclin Es, Cyclin Et, G1/S-specific cyclin-E1, G1/s-specific cyclin e, Cyclin E
ACCESSION NO.:	P24864
PROTEIN GI NO.:	3041657
OFFICIAL SYMBOL:	CCNE1
GENE ID:	898

Background

FOR RESEARCH USE ONLY

December 13, 2016