



PEBP1 Antibody

CATALOG NUMBER: 70-481

Specifications

SPECIES REACTIVITY:	Human, Mouse
TESTED APPLICATIONS:	ELISA, IHC, WB
APPLICATIONS:	PEBP1 Antibody can be used for ELISA starting at 1:1000, and Immunohistochemistry in paraffin embedded tissues starting at 10 ug/mL,
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	KLH-conjugated synthetic peptide between amino acids 1-30 from N-terminal region of human PBP.
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Protein G Column
BUFFER:	PBS, 0.09% sodium azide
CONCENTRATION:	0.25 mg/ml
STORAGE CONDITIONS:	Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Polyclonal
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	PEBP1, HCNP, HCNPPp, PBP, Prostatic binding protein, Raf kinase inhibitor protein, Raf kinase inhibitory protein, Prostatic-binding protein, Neuropolypeptide h3, PEBP, PEBP-1, RKIP
ACCESSION NO.:	P30086
PROTEIN GI NO.:	1352726
OFFICIAL SYMBOL:	PEBP1
GENE ID:	5037

Background

FOR RESEARCH USE ONLY

December 13, 2016