



RNF144A / RNF144 Antibody

CATALOG NUMBER: 70-514

Specifications

SPECIES REACTIVITY:	Human, Mouse
TESTED APPLICATIONS:	ELISA, IHC, WB
APPLICATIONS:	ELISA, IHC-P, WB
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	RNF144A Antibody detects endogenous levels of total RNF144A protein.
IMMUNOGEN:	Synthetic peptide from human RNF144A.
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Immunoaffinity Chromatography
BUFFER:	PBS (without Mg2+, Ca2+), pH 7.4, 150 mM sodium chloride, 0.02% sodium azide, 50% glycerol
STORAGE CONDITIONS:	Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Polyclonal
ISOTYPE:	IgG
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	RNF144A, KIAA0161, Ring finger protein 144, Ring finger protein 144A, UbcM4-interacting protein 4, RNF144, UBCE7IP4
ACCESSION NO.:	P50876
PROTEIN GI NO.:	160358924
OFFICIAL SYMBOL:	RNF144A
GENE ID:	9781

Background

FOR RESEARCH USE ONLY

December 13, 2016