



KRT19 / Cytokeratin 19 Antibody

CATALOG NUMBER: 70-661

Specifications

SPECIES REACTIVITY:	Human, Mouse, Rat
TESTED APPLICATIONS:	ELISA, IHC, WB
APPLICATIONS:	ELISA, IHC-P (1:200), WB
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	Keratin 19 Antibody detects endogenous levels of total Keratin 19 protein.
IMMUNOGEN:	Synthetic peptide
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Immunoaffinity Chromatography
BUFFER:	PBS (without Mg2+, Ca2+), pH 7.4, 150 mM sodium chloride, 0.02% sodium azide, 50% glycerol
STORAGE CONDITIONS:	Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Polyclonal
ISOTYPE:	IgG
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	KRT19, CK19, Cytokeratin 19, Cytokeratin-19, Keratin 19, Keratin-19, CK-19, K19, K1CS, Keratin, type I, 40-kd
ACCESSION NO.:	P08727
PROTEIN GI NO.:	311033484
OFFICIAL SYMBOL:	KRT19
GENE ID:	3880

Background

FOR RESEARCH USE ONLY

December 13, 2016