



prosci-inc.com



ProSci Incorporated
12170 Flint Place
Poway, CA 92064



Toll Free: +1 (888) 513 9525
Local: +1 (858) 513 2638
Fax: +1 (858) 513 2692

techsupport@prosci-inc.com

SOD2 Antibody

CATALOG NUMBER: 70-669

Specifications

SPECIES REACTIVITY:	Human, Mouse, Rat
TESTED APPLICATIONS:	IHC, IP, WB
APPLICATIONS:	SOD2 Antibody can be used for Immunohistochemistry in paraffin embedded tissues starting at 1:200, Immunoprecipitation and Western Blotting starting at 1:2000.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Recombinant human protein purified from E. coli
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Purified
BUFFER:	HEPES with 0.15M NaCl, 0.01% BSA, 0.03% sodium azide, and 50% glycerol
STORAGE CONDITIONS:	Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Polyclonal
ISOTYPE:	IgG
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	SOD2, IPOB, MVCD6, Indophenoloxidase B, Mn superoxide dismutase, MNSOD, Mangano-superoxide dismutase
ACCESSION NO.:	P04179
PROTEIN GI NO.:	134665
OFFICIAL SYMBOL:	SOD2
GENE ID:	6648

Background

FOR RESEARCH USE ONLY

December 13, 2016