



RHOH Antibody

CATALOG NUMBER: 70-672

Specifications

SPECIES REACTIVITY:	Human, Mouse, Rat
TESTED APPLICATIONS:	ELISA, IF, IHC, WB
APPLICATIONS:	ELISA, IF, IHC-P (1:200), WB
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	RhoH Antibody detects endogenous levels of total RhoH protein.
IMMUNOGEN:	Synthetic peptide from human RhoH.
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Immunoaffinity Chromatography
BUFFER:	PBS (without Mg2+, Ca2+), pH 7.4, 150 mM sodium chloride, 0.02% sodium azide, 50% glycerol
STORAGE CONDITIONS:	Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Polyclonal
ISOTYPE:	IgG
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	RHOH, ARHH, TTF, translocation three four, TTF, GTP-binding protein TTF, Ras homolog family member H
ACCESSION NO.:	Q15669
PROTEIN GI NO.:	2500200
OFFICIAL SYMBOL:	RHOH
GENE ID:	399

Background

FOR RESEARCH USE ONLY

December 13, 2016