



prosci-inc.com



ProSci Incorporated
12170 Flint Place
Poway, CA 92064



Toll Free: +1 (888) 513 9525
Local: +1 (858) 513 2638
Fax: +1 (858) 513 2692

techsupport@prosci-inc.com

PPP3CA / Calcineurin A Antibody

CATALOG NUMBER: 70-699

Specifications

SPECIES REACTIVITY:	Human, Mouse
TESTED APPLICATIONS:	ELISA, IHC, WB
APPLICATIONS:	GLUD1 Antibody can be used for ELISA starting at 1:4000 - 1:16000, and Immunohistochemistry in paraffin embedded tissues starting at 1:100,
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	KLH-conjugated synthetic peptide between amino acids 21-51 from N-terminal region of human Calcineurin (PPP3CA).
HOST SPECIES:	Rabbit

Properties

PURIFICATION:	Ammonium Sulfate Precipitation
BUFFER:	PBS, 0.09% sodium azide
CONCENTRATION:	0.25 mg/ml
STORAGE CONDITIONS:	Antibody may be stored short term at 4°C, long term aliquot and store at -20°C, avoid freeze thaw cycles.
CLONALITY:	Polyclonal
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	PPP3CA, Calcineurin A, CALN, CALNA, CALNA1, CNA1, PPP2B, Calcineurin A alpha, CAM-PRP catalytic subunit, CCN1, CNA, CNA alpha, pp2b-alpha
ACCESSION NO.:	Q08209
PROTEIN GI NO.:	1352673
OFFICIAL SYMBOL:	PPP3CA
GENE ID:	5530

Background

FOR RESEARCH USE ONLY

December 13, 2016