



TRIM11 Antibody

CATALOG NUMBER: 46-517

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA
APPLICATIONS:	ELISA: Antibody detection limit dilution 1:16,000.
IMMUNOGEN:	TRIM11 antibody was raised against a 14 amino acid synthetic peptide near the C-Terminus of TRIM11.
HOST SPECIES:	Goat

Properties

PURIFICATION:	TRIM11 antibody was purified from goat serum by ammonium sulphate precipitation followed by antigen affinity chromatography using the immunizing peptide.
PHYSICAL STATE:	Liquid
BUFFER:	TRIM11 antibody is supplied in Tris saline, 0.02% sodium azide, pH 7.3 with 0.5% bovine serum albumin.
CONCENTRATION:	500 ug/mL
STORAGE CONDITIONS:	Aliquot and store at -20°C. Minimize freezing and thawing.
CLONALITY:	Polyclonal
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	TRIM11, BIA1, RNF92, tripartite motif-containing 11
ACCESSION NO.:	NP_660215
PROTEIN GI NO.:	21630277
OFFICIAL SYMBOL:	TRIM11
GENE ID:	81559

Background

REFERENCES:	1) Reymond A, Meroni G, Fantozzi A, Merla G, Cairo S, Luzi L, Riganelli D, Zanaria E, Messali S, Cainarca S, Guffanti A, Minucci S, Pelicci PG, Ballabio A. The tripartite motif family identifies cell compartments. EMBO J. 2001 May 1;20(9):2140-51.
--------------------	---

FOR RESEARCH USE ONLY

December 13, 2016