



TSPYL2 Antibody

CATALOG NUMBER: 42-954

Specifications

SPECIES REACTIVITY:

TESTED APPLICATIONS: ELISA

APPLICATIONS: ELISA: antibody detection limit dilution 1:4000. Western Blot: Preliminary experiments in Human, Mouse and Rat Testis lysates gave no specific signal but low background (at antibody concentration up to 1ug/ml). We would appreciate any feedback from people in the field - have any results been reported w

IMMUNOGEN: TSPYL2 Antibody was raised against a 12 amino acid sequence near the N-Terminus of TSPYL2 (aa2-13).

HOST SPECIES: Goat

Properties

PURIFICATION: Antibody was purified from goat serum by ammonium sulphate precipitation followed by antigen affinity chromatography using the immunizing peptide.

PHYSICAL STATE: Liquid

BUFFER: TSPYL2 antibody is supplied in Tris saline, 0.02% sodium azide, pH 7.3 with 0.5% bovine serum albumin.

CONCENTRATION: 500 ug/mL

STORAGE CONDITIONS: Aliquot and store at -20°C. Minimize freezing and thawing.

CLONALITY: Polyclonal

CONJUGATE: Unconjugated

Additional Info

ALTERNATE NAMES: TSPYL2, TSPY-like protein 2, TSPY-like 2, TSPX, testis-specific Y-encoded-like protein 2, testis-specific protein Y encoded-like 2, SE204, nuclear protein of 79 kDa, NP79, HRIHFB2216, differentially-expressed nucleolar TGF-beta1 target protein, differentially expressed nucleolar TGF-beta1 target, DENTT, cutaneous T-cell lymphoma-associated tumor antigen se20-4, cutaneous T-cell lymphoma-associated antigen se20-4, CTCL-associated antigen se20-4, CTCL tumor antigen se20-4, CTCL, CINAP, cell division autoantigen 1, CDA1, CASK-interacting nucleosome assembly protein

ACCESSION NO.: NP_071400.1

PROTEIN GI NO.: 11545835

OFFICIAL SYMBOL: TSPYL2

GENE ID: 64061

Background

FOR RESEARCH USE ONLY

December 13, 2016