



zgc 63629 Antibody

CATALOG NUMBER: 43-010

Specifications

SPECIES REACTIVITY:

TESTED APPLICATIONS: ELISA

APPLICATIONS: ELISA: antibody detection limit dilution 1:128000. Western Blot: Not yet tested. At this stage we are dependent on researchers in the field for further characterization of this product. Therefore we cannot recommend an optimal concentration and the antibody is an aspiring product. We would appreciate any

IMMUNOGEN: zgc 63629 antibody was raised against a 15 amino acid peptide near the internal region of zgc 63629 (Danio rerio aa393-407).

HOST SPECIES: Goat

Properties

PURIFICATION: zgc 63629 antibody was purified from goat serum by ammonium sulphate precipitation followed by antigen affinity chromatography using the immunizing peptide.

PHYSICAL STATE: Liquid

BUFFER: zgc 63629 antibody is supplied in Tris saline, 0.02% sodium azide, pH 7.3 with 0.5% bovine serum albumin.

CONCENTRATION: 500 ug/mL

STORAGE CONDITIONS: Aliquot and store at -20°C. Minimize freezing and thawing.

CLONALITY: Polyclonal

CONJUGATE: Unconjugated

Additional Info

ALTERNATE NAMES: EGF, latrophilin and seven transmembrane domain containing 1, Eltd1, zgc:63629 , zgc:63629, wu:fd10a02

ACCESSION NO.: NP_998532.1

PROTEIN GI NO.: 47087037

OFFICIAL SYMBOL: eltd1

GENE ID: 406676

Background

FOR RESEARCH USE ONLY

December 13, 2016