



BCL2L15 Antibody

CATALOG NUMBER: 42-323

Specifications

SPECIES REACTIVITY:

TESTED APPLICATIONS: ELISA

APPLICATIONS: ELISA: Antibody detection limit dilution 1:8000.

IMMUNOGEN: BCL2L15 antibody was raised against a 10 amino acid synthetic peptide near the internal region of BCL2L15.

HOST SPECIES: Goat

Properties

PURIFICATION: BCL2L15 antibody was purified from goat serum by ammonium sulphate precipitation followed by antigen affinity chromatography using the immunizing peptide.

PHYSICAL STATE: Liquid

BUFFER: BCL2L15 antibody is supplied in Tris saline, 0.02% sodium azide, pH 7.3 with 0.5% bovine serum albumin.

CONCENTRATION: 500 ug/mL

STORAGE CONDITIONS: Aliquot and store at -20°C. Minimize freezing and thawing.

CLONALITY: Polyclonal

CONJUGATE: Unconjugated

Additional Info

ALTERNATE NAMES: BCL2L15, pro-apoptotic Bcl-2 protein, FLJ22588, C1orf178, Bfk, BCL2-like 15

ACCESSION NO.: NP_001010922.1

PROTEIN GI NO.: 58219054

OFFICIAL SYMBOL: BCL2L15

GENE ID: 440603

Background

FOR RESEARCH USE ONLY

December 13, 2016