



Hes7 Antibody

CATALOG NUMBER: 42-351

Specifications

SPECIES REACTIVITY:

TESTED APPLICATIONS: ELISA, WB

APPLICATIONS: ELISA: Antibody detection limit dilution 1:16000. Western Blot: Preliminary experiments in mouse fetal liver and fetal skeletal muscle lysates gave no specific signal but low background (at antibody concentration up to 1 ug/mL).

IMMUNOGEN: Hes7 antibody was raised against a 15 amino acid synthetic peptide near the internal region of Hes7.

HOST SPECIES: Goat

Properties

PURIFICATION: Hes7 antibody was purified from goat serum by ammonium sulphate precipitation followed by antigen affinity chromatography using the immunizing peptide.

PHYSICAL STATE: Liquid

BUFFER: Hes7 antibody is supplied in Tris saline, 0.02% sodium azide, pH 7.3 with 0.5% bovine serum albumin.

CONCENTRATION: 500 ug/mL

STORAGE CONDITIONS: Aliquot and store at -20°C. Minimize freezing and thawing.

CLONALITY: Polyclonal

CONJUGATE: Unconjugated

Additional Info

ALTERNATE NAMES: transcription factor HES-7, mHes7, bHLH factor Hes7, OTTMUSP00000006176, bHLHb37, hairy and enhancer of split 7 (Drosophila), Hes7, BHLHB37

ACCESSION NO.: NP_149030.2

PROTEIN GI NO.: 61098129

OFFICIAL SYMBOL: Hes7

GENE ID: 84667

Background

FOR RESEARCH USE ONLY

December 13, 2016