



BICC1 Antibody

CATALOG NUMBER: 42-507

Specifications

SPECIES REACTIVITY:

TESTED APPLICATIONS: ELISA

APPLICATIONS: ELISA: antibody detection limit dilution 1:1000. Western Blot: Preliminary experiments in Human Brain (Cerebellum), Kidney, Lung and Pancreas lysates, and in lysates of Mouse fetal Brain and cell line A549 gave no specific signal but low background (at antibody concentration up to 2ug/ml). We would app

IMMUNOGEN: BICC1 antibody was raised against a 12 amino acid synthetic peptide near the internal region of BICC1.

HOST SPECIES: Goat

Properties

PURIFICATION: BICC1 antibody was purified from goat serum by ammonium sulphate precipitation followed by antigen affinity chromatography using the immunizing peptide.

PHYSICAL STATE: Liquid

BUFFER: BICC1 antibody is supplied in Tris saline, 0.02% sodium azide, pH 7.3 with 0.5% bovine serum albumin.

CONCENTRATION: 500 ug/mL

STORAGE CONDITIONS: Aliquot and store at -20°C. Minimize freezing and thawing.

CLONALITY: Polyclonal

CONJUGATE: Unconjugated

Additional Info

ALTERNATE NAMES: BICC1, DKFZp686l21119, bicaudal C homolog 1 (Drosophila), bicaudal C homolog 1, BICC, CYSRD

ACCESSION NO.: NP_001073981.1

PROTEIN GI NO.: 122937472

OFFICIAL SYMBOL: BICC1

GENE ID: 80114

Background

FOR RESEARCH USE ONLY

December 13, 2016