



FBXO4 Antibody

CATALOG NUMBER: 42-543

Specifications

SPECIES REACTIVITY:

TESTED APPLICATIONS: ELISA

APPLICATIONS: ELISA: antibody detection limit dilution 1:8000. Western Blot: Preliminary experiments gave an approx 48kDa band in Human Heart ysates after 1ug/ml antibody staining. Please note that currently we cannot find an explanation in the literature for the band we observe given the calculated size of 44.1kDa

SPECIFICITY: This antibody is expected to recognize isoform 1 and 2 (NP_036308.1; NP_277019.1).

IMMUNOGEN: FBXO4 antibody was raised against a 13 amino acid synthetic peptide near the internal region of FBXO4.

HOST SPECIES: Goat

Properties

PURIFICATION: FBXO4 antibody was purified from goat serum by ammonium sulphate precipitation followed by antigen affinity chromatography using the immunizing peptide.

PHYSICAL STATE: Liquid

BUFFER: FBXO4 antibody is supplied in Tris saline, 0.02% sodium azide, pH 7.3 with 0.5% bovine serum albumin.

CONCENTRATION: 500 ug/mL

STORAGE CONDITIONS: Aliquot and store at -20°C. Minimize freezing and thawing.

CLONALITY: Polyclonal

CONJUGATE: Unconjugated

Additional Info

ALTERNATE NAMES: FBXO4, FLJ10141, FBX4, F-box protein Fbx4, F-box protein 4, F-box only protein 4, DKFZp547N213

ACCESSION NO.: NP_036308.1, NP_277019.1

PROTEIN GI NO.: 15834619

OFFICIAL SYMBOL: FBXO4

GENE ID: 26272

Background

FOR RESEARCH USE ONLY

December 13, 2016