



PEX12 Antibody

CATALOG NUMBER: 42-599

Specifications

SPECIES REACTIVITY:

TESTED APPLICATIONS: ELISA

APPLICATIONS: ELISA: antibody detection limit dilution 1:8000. Western Blot: Preliminary experiments in Human, Mouse and Rat Liver lysates gave no specific signal but low background (at antibody concentration up to 1ug/ml). We would appreciate any feedback from people in the field - have any results been reported w

IMMUNOGEN: PEX12 antibody was raised against a 12 amino acid synthetic peptide near the C-Terminus of PEX12.

HOST SPECIES: Goat

Properties

PURIFICATION: PEX12 antibody was purified from goat serum by ammonium sulphate precipitation followed by antigen affinity chromatography using the immunizing peptide.

PHYSICAL STATE: Liquid

BUFFER: PEX12 antibody is supplied in Tris saline, 0.02% sodium azide, pH 7.3 with 0.5% bovine serum albumin.

CONCENTRATION: 500 ug/mL

STORAGE CONDITIONS: Aliquot and store at -20°C. Minimize freezing and thawing.

CLONALITY: Polyclonal

CONJUGATE: Unconjugated

Additional Info

ALTERNATE NAMES: PEX12, peroxisome assembly protein 12, peroxisome assembly factor 3, peroxisomal biogenesis factor 12, peroxin 12, PAF-3, PAF3

ACCESSION NO.: NP_000277.1

PROTEIN GI NO.: 4505721

OFFICIAL SYMBOL: PEX12

GENE ID: 5193

Background

FOR RESEARCH USE ONLY

December 13, 2016