



## BIRC6 Antibody

CATALOG NUMBER: 42-664

### Specifications

#### SPECIES REACTIVITY:

**TESTED APPLICATIONS:** ELISA

**APPLICATIONS:** ELISA: antibody detection limit dilution 1:64000. Western Blot: Preliminary experiments gave bands at approx 90kDa and 70kDa in lysates of cell lines A431 and HeLa after 0.1ug/ml antibody staining. Please note that currently we cannot find an explanation in the literature for the bands we observe given

**IMMUNOGEN:** BIRC6 antibody was raised against a 12 amino acid synthetic peptide near the internal region of BIRC6 (aa 4724 -4735).

**HOST SPECIES:** Goat

### Properties

**PURIFICATION:** BIRC6 antibody was purified from goat serum by ammonium sulphate precipitation followed by antigen affinity chromatography using the immunizing peptide.

**PHYSICAL STATE:** Liquid

**BUFFER:** BIRC6 antibody is supplied in Tris saline, 0.02% sodium azide, pH 7.3 with 0.5% bovine serum albumin.

**CONCENTRATION:** 500 ug/mL

**STORAGE CONDITIONS:** Aliquot and store at -20°C. Minimize freezing and thawing.

**CLONALITY:** Polyclonal

**CONJUGATE:** Unconjugated

### Additional Info

**ALTERNATE NAMES:** BIRC6, ubiquitin-conjugating BIR-domain enzyme apollon, KIAA1289, FLJ13786, FLJ13726, BRUCE, baculoviral IAP repeat-containing 6, APOLLON

**ACCESSION NO.:** NP\_057336.3

**PROTEIN GI NO.:** 153792694

**OFFICIAL SYMBOL:** BIRC6

**GENE ID:** 57448

### Background

FOR RESEARCH USE ONLY

December 13, 2016