



## PCBP3 Antibody

CATALOG NUMBER: 42-939

### Specifications

#### SPECIES REACTIVITY:

**TESTED APPLICATIONS:** ELISA

**APPLICATIONS:** ELISA: antibody detection limit dilution 1:32000. Western Blot: Preliminary experiments in Human Testis, Adipose, Lung and several cel line lysates gave no specific signal but low background (at antibody concentration up to 2ug/ml). We would appreciate any feedback from people in the field - have any re

**SPECIFICITY:** This antibody is expected to recognize both reported isoforms (NP\_065389.2; NP\_001123613.1). No cross-reactivity wth other PCBP proteins are expected.

**IMMUNOGEN:** PCBP3 Antibody was raised against a 15 amino acid sequence near the N-Terminus of PCBP3 (aa14-28).

**HOST SPECIES:** Goat

### Properties

**PURIFICATION:** Antibody was purified from goat serum by ammonium sulphate precipitation followed by antigen affinity chromatography using the immunizing peptide.

**PHYSICAL STATE:** Liquid

**BUFFER:** PCBP3 antibody is supplied in Tris saline, 0.02% sodium azide, pH 7.3 with 0.5% bovine serum albumin.

**CONCENTRATION:** 500 ug/mL

**STORAGE CONDITIONS:** Aliquot and store at -20°C. Minimize freezing and thawing.

**CLONALITY:** Polyclonal

**CONJUGATE:** Unconjugated

### Additional Info

**ALTERNATE NAMES:** PCBP3, poly(rC)-binding protein 3, poly(rC) binding protein 3, OTTHUMP00000115469, OTTHUMP00000115468, OTTHUMP00000115467, OTTHUMP00000115466, OTTHUMP00000115465, OTTHUMP00000115464, ALPHA-CP3

**ACCESSION NO.:** NP\_065389.2, NP\_001123613.1

**PROTEIN GI NO.:** 194306631

**OFFICIAL SYMBOL:** PCBP3

**GENE ID:** 54039

### Background

FOR RESEARCH USE ONLY

December 13, 2016