



WFDC2 Antibody

CATALOG NUMBER: 42-944

Specifications

SPECIES REACTIVITY:

TESTED APPLICATIONS: ELISA

APPLICATIONS: ELISA: antibody detection limit dilution 1:2000. Western Blot: Not yet tested - our routinely used western blotting protocol does not allow detection of proteins smaller than the calculated size of 13kDa according to the precursor NP_006094.3. Therefore we cannot recommend an optimal concentration and

IMMUNOGEN: WFDC2 Antibody was raised against a 14 amino acid sequence near the internal region of WFDC2.

HOST SPECIES: Goat

Properties

PURIFICATION: Antibody was purified from goat serum by ammonium sulphate precipitation followed by antigen affinity chromatography using the immunizing peptide.

PHYSICAL STATE: Liquid

BUFFER: WFDC2 antibody is supplied in Tris saline, 0.02% sodium azide, pH 7.3 with 0.5% bovine serum albumin.

CONCENTRATION: 500 ug/mL

STORAGE CONDITIONS: Aliquot and store at -20°C. Minimize freezing and thawing.

CLONALITY: Polyclonal

CONJUGATE: Unconjugated

Additional Info

ALTERNATE NAMES: WFDC2, WAP5, WAP four-disulfide core domain 2, WAP domain containing protein HE4-V4, MGC57529, major epididymis-specific, whey-acidic protein type, four-disulfide core, epididymal secretory protein E4, epididymal protein 4, EDDM4, dJ461P17.6

ACCESSION NO.: NP_006094.3

PROTEIN GI NO.: 56699495

OFFICIAL SYMBOL: WFDC2

GENE ID: 10406

Background

FOR RESEARCH USE ONLY

December 13, 2016