



LSM3 Antibody

CATALOG NUMBER: 43-058

Specifications

SPECIES REACTIVITY:

TESTED APPLICATIONS: ELISA

APPLICATIONS: ELISA: antibody detection limit dilution 1:128000. Western Blot: Preliminary experiments in Human and Rodent Spleen lysates gave no specific signal but low background (at antibody concentration up to 1ug/ml). We would appreciate any feedback from people in the field - have any results been reported with

IMMUNOGEN: LSM3 antibody was raised against a 13 amino acid peptide near the internal region of LSM3.

HOST SPECIES: Goat

Properties

PURIFICATION: LSM3 antibody was purified from goat serum by ammonium sulphate precipitation followed by antigen affinity chromatography using the immunizing peptide.

PHYSICAL STATE: Liquid

BUFFER: LSM3 antibody is supplied in Tris saline, 0.02% sodium azide, pH 7.3 with 0.5% bovine serum albumin.

CONCENTRATION: 500 ug/mL

STORAGE CONDITIONS: Aliquot and store at -20°C. Minimize freezing and thawing.

CLONALITY: Polyclonal

CONJUGATE: Unconjugated

Additional Info

ALTERNATE NAMES: LSM3, LSM3 homolog, U6 small nuclear RNA associated (S. cerevisiae), OTTHUMP00000160275, SMX4, U6 snRNA-associated Sm-like protein LSm3, USS2, YLR438C

ACCESSION NO.: NP_055278.1

PROTEIN GI NO.: 7657315

OFFICIAL SYMBOL: LSM3

GENE ID: 27258

Background

FOR RESEARCH USE ONLY

December 13, 2016