



REXO1 Antibody

CATALOG NUMBER: 46-282

Specifications

SPECIES REACTIVITY:

TESTED APPLICATIONS: ELISA

APPLICATIONS: ELISA: Antibody detection limit dilution 1:8,000.

IMMUNOGEN: REXO1 antibody was raised against a 10 amino acid synthetic peptide near the C-Terminus of REXO1.

HOST SPECIES: Goat

Properties

PURIFICATION: REXO1 antibody was purified from goat serum by ammonium sulphate precipitation followed by antigen affinity chromatography using the immunizing peptide.

PHYSICAL STATE: Liquid

BUFFER: REXO1 antibody is supplied in Tris saline, 0.02% sodium azide, pH 7.3 with 0.5% bovine serum albumin.

CONCENTRATION: 500 ug/mL

STORAGE CONDITIONS: Aliquot and store at -20°C. Minimize freezing and thawing.

CLONALITY: Polyclonal

CONJUGATE: Unconjugated

Additional Info

ALTERNATE NAMES: REXO1, REX1, RNA exonuclease 1 homolog (S. cerevisiae), ELOABP1, EloA-BP1, KIAA1138, TCEB3BP1, elongin A binding protein 1, transcription elongation factor B polypeptide 3 binding protein 1

ACCESSION NO.: NP_065746.2

PROTEIN GI NO.: 37655181

OFFICIAL SYMBOL: REXO1

GENE ID: 57455

Background

REFERENCES: 1) Palmqvist L, Glover CH, Hsu L, Lu M, Bossen B, Piret JM, Humphries RK, Helgason CD. Correlation of murine embryonic stem cell gene expression profiles with functional measures of pluripotency. Stem Cells. 2005 May;23(5):663-80.

FOR RESEARCH USE ONLY

December 13, 2016